

D-160

Handheld Homogenizer

Features

- Portable, lightweight with ergonomic design ideal for manual operations
- Processing volumes from 0.1-50mL or 1-250mL
- Variable speed from 8,000 to 32,000 rpm
- 316L stainless steel shafts are fully autoclavable
- Interchangeable shafts for easy dismantling and cleaning

Applications

Designed for rapidly homogenize, emulsify, suspend and disrupt biological samples like tissue of animal, bacteria, yeast, plant samples, etc. in liquids. Ideal for samples from 0.1mL to 250mL depending on shaft chosen.



Specifications	D-160
Speed range	8000-32000rpm
Max linear velocity	6.3、10、14 m/sec
Speed level	10 stage
Working volume [H ₂ O]	0.1-50mL (Dispersing shaft DS-160/5)
	1-150mL (Dispersing shaft DS-160/7)
	1-250mL (Dispersing shaft DS-160/10)
Max. viscosity	5000mPa·s
Material of Dispersing Shaft	SS 316L stainless steel, PTFE
Noise Level	72 dB(A)
Protection class	IP20
Voltage, Frequency	110-120V/60Hz 220-240V/50-60Hz
Power	160W
Motor Type	AC carbon brush motor
Dimension [WxDxH]	45mm x 55mm x 190mm
Weight	0.54 kg
Permissible ambient temperature and humidity	0-40°C, 85%RH

DS-160/5 Cat. No.18900543

Volume 0.1-50mL
Max. Circum. Speed 6.3m/sec
Material: 316L stainless steel
Application: small amounts of solid liquid mixed
Function: dispersing tool for solid/liquid media



DS-160/7 Cat. No.18900815

Volume 1-150mL
Max. Circum. Speed 10m/sec
Material: 316L stainless steel
Application: small amounts of solid liquid mixed
Function: dispersing tool for solid/liquid media



DS-160/10 Cat. No.18900544

Volume 1-250mL
Max. Circum. Speed 14m/sec
Material: 316L stainless steel
Application: small amounts of solid liquid mixed
Function: dispersing tool for solid/liquid media

